

T30-N40160-6C Cut Sheet



ProSense bi-metal dial thermometer, 3in diameter, 6in insertion length, -40 to 160 deg F/-40 to 70 deg C, 1/2in male NPT process connection, center back mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T30-N40160-6C>

Technical Specifications

Brand	ProSense
Item	Bi-metal dial thermometer
Diameter	3in
Insertion Length	6in
Scale	-40 to 160 deg F/-40 to 70 deg C
Process Connection	1/2in male NPT
Mounting	Center back

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/T30-N40160-6C.pdf>
See store item page for other formats.