

T30R-FD-34-120A Cut Sheet



ProSense off-delay relay timer, 0.1 to 10 hours timing range, 120 VAC/VDC operating voltage, 30A contact rating, (1) SPDT timed relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T30R-FD-34-120A>

Technical Specifications

Brand	ProSense
Item	Relay timer
Timer Type	Off-delay
Timing Range	0.1 to 10 hours
Operating Voltage	120 VAC/VDC
Timer Output Type(s)	(1) SPDT timed relay
Timer Function(s)	off-delay
Contact Rating	30A
Mounting	Surface
Connector Type	1/4in male quick-connect terminal

Agency Approvals

UL Listed File #	None
UL Recognized File #	E191059
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/T30R-FD-34-120A.pdf>
See store item page for other formats.