

# T30R-ND-33-24AD Cut Sheet



ProSense on-delay relay timer, 1 to 100 minutes timing range, 24 VAC/VDC operating voltage, 30A contact rating, (1) SPDT timed relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T30R-ND-33-24AD>

## Technical Specifications

|                             |                                   |
|-----------------------------|-----------------------------------|
| <b>Brand</b>                | ProSense                          |
| <b>Item</b>                 | Relay timer                       |
| <b>Timer Type</b>           | On-delay                          |
| <b>Timing Range</b>         | 1 to 100 minutes                  |
| <b>Operating Voltage</b>    | 24 VAC/VDC                        |
| <b>Timer Output Type(s)</b> | (1) SPDT timed relay              |
| <b>Timer Function(s)</b>    | on-delay                          |
| <b>Contact Rating</b>       | 30A                               |
| <b>Mounting</b>             | Surface                           |
| <b>Connector Type</b>       | 1/4in male quick-connect terminal |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | None  |
| <b>UL Recognized File #</b> | E191059   |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/T30R-ND-33-24AD.pdf>  
See store item page for other formats.