

T30R-RC-30-24AD Cut Sheet



ProSense cyclic relay timer, 0.1 to 10 seconds timing range, 24 VAC/VDC operating voltage, 30A contact rating, (1) SPDT timed relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T30R-RC-30-24AD>

Technical Specifications

| | |
|-----------------------------|-----------------------------------|
| Brand | ProSense |
| Item | Relay timer |
| Timer Type | Cyclic |
| Timing Range | 0.1 to 10 seconds |
| Operating Voltage | 24 VAC/VDC |
| Timer Output Type(s) | (1) SPDT timed relay |
| Timer Function(s) | cyclic |
| Contact Rating | 30A |
| Mounting | Surface |
| Connector Type | 1/4in male quick-connect terminal |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | E191059 |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/T30R-RC-30-24AD.pdf>
See store item page for other formats.