

# T30R-RC-32-120A Cut Sheet



ProSense cyclic relay timer, 0.1 to 10 minutes timing range, 120 VAC/VDC operating voltage, 30A contact rating, (1) SPDT timed relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T30R-RC-32-120A>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Relay timer
<b>Timer Type</b>	Cyclic
<b>Timing Range</b>	0.1 to 10 minutes
<b>Operating Voltage</b>	120 VAC/VDC
<b>Timer Output Type(s)</b>	(1) SPDT timed relay
<b>Timer Function(s)</b>	cyclic
<b>Contact Rating</b>	30A
<b>Mounting</b>	Surface
<b>Connector Type</b>	1/4in male quick-connect terminal

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E191059
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/T30R-RC-32-120A.pdf>  
See store item page for other formats.