

T483616RT Cut Sheet



AttaBox Triton series enclosure, NEMA 1/3R, 48 x 36 x 16in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (3) twist-lock latches, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T483616RT>

Technical Specifications

Brand	AttaBox	Dual Access	No
Item	Enclosure	Knockouts	No
Series	Triton	Material	Fiberglass reinforced polyester
Subpanel	Purchase subpanel separately	Color	Gray
Slope Top	No	Cover Type	Single-door
NEMA Rating	1/3R	Hinge Type	Continuous hinge
Nominal Enclosure Height	48in	Number of Hinges Per Door	1
Nominal Enclosure Width	36in	Latch Type	(3) twist-lock latches
Nominal Enclosure Depth	16in	Padlock Attachment Type	Padlock hasp and staple
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	Yes	Keylocking	No
Integral Mounting Flange	No		

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	none
UL Hazardous File #	none
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/T483616RT.pdf>
See store item page for other formats.