

T50-0250-9A Cut Sheet



ProSense bi-metal dial thermometer, 5in diameter, 9in insertion length, 0 to 250 deg F/-18 to 120 deg C, 1/2in male NPT process connection, center back, adjustable angle mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T50-0250-9A>

Technical Specifications

Brand	ProSense
Item	Bi-metal dial thermometer
Diameter	5in
Insertion Length	9in
Scale	0 to 250 deg F/-18 to 120 deg C
Process Connection	1/2in male NPT
Mounting	Center back, adjustable angle

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/T50-0250-9A.pdf>
See store item page for other formats.