

# T50-150750-25A Cut Sheet



ProSense bi-metal dial thermometer, 5in diameter, 2-1/2in insertion length, 150 to 750 deg F/70 to 400 deg C, 1/2in male NPT process connection, center back, adjustable angle mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T50-150750-25A>

---

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Bi-metal dial thermometer
<b>Diameter</b>	5in
<b>Insertion Length</b>	2 1/2in
<b>Scale</b>	150 to 750 deg F/70 to 400 deg C
<b>Process Connection</b>	1/2in male NPT
<b>Mounting</b>	Center back, adjustable angle

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

---

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/T50-150750-25A.pdf>  
See store item page for other formats.