

# T50-50500-6A Cut Sheet



ProSense bi-metal dial thermometer, 5in diameter, 6in insertion length, 50 to 500 deg F/10 to 260 deg C, 1/2in male NPT process connection, center back, adjustable angle mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T50-50500-6A>

## Technical Specifications

|                    |                                 |
|--------------------|---------------------------------|
| Brand              | ProSense                        |
| Item               | Bi-metal dial thermometer       |
| Diameter           | 5in                             |
| Insertion Length   | 6in                             |
| Scale              | 50 to 500 deg F/10 to 260 deg C |
| Process Connection | 1/2in male NPT                  |
| Mounting           | Center back, adjustable angle   |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |