

T6612CHSS Cut Sheet



Wiegmann wiring trough, 6 x 6 x 12in (HxDxL), NEMA 1/4/4X/12, 304 stainless steel, No. 3 intermediate polished finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T6612CHSS>

Technical Specifications

Brand	Wiegmann
Item	Wiring trough
NEMA Rating	1/4/4X/12
IP Rating	IP66
Nominal Enclosure Dimensions	6 x 12 x 6in (HxWxD)
Enclosure Height	6.22in
Enclosure Depth	6.25in
Enclosure Length	12.31in

Integral Mounting Feet	Yes
Knockouts	No
Material	304 stainless steel
Finish	No. 3 intermediate polished
Cover Type	Single-door
Latch Type	Stainless steel clamps
Padlockable	No

Agency Approvals

UL Listed File #	E32576
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/T6612CHSS.pdf>
See store item page for other formats.