

# T6648CH Cut Sheet

Wiegmann wiring trough, 6 x 6 x 48in (HxDxL), NEMA 4, carbon steel, ANSI 61 gray, powder coat finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T6648CH>

## Technical Specifications

Brand	Wiegmann
Item	Wiring trough
NEMA Rating	4
Nominal Enclosure Dimensions	6 x 48 x 6in (HxWxD)
Enclosure Height	6.22in
Enclosure Depth	6.25in
Enclosure Length	48.31in

Integral Mounting Feet	Yes
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Latch Type	Plated steel clamps

## Agency Approvals

UL Listed File #	E32576
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/T6648CH.pdf>  
See store item page for other formats.