

# T8848CHSS Cut Sheet

Wiegmann wiring trough, 8 x 8 x 48in (HxDxL), NEMA 1/4/4X/12, 304 stainless steel, No. 3 intermediate polished finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T8848CHSS>

## Technical Specifications

Brand	Wiegmann
Item	Wiring trough
NEMA Rating	1/4/4X/12
IP Rating	IP66
Nominal Enclosure Dimensions	8 x 48 x 8in (HxWxD)
Enclosure Height	8.22in
Enclosure Depth	8.25in
Enclosure Length	48.31in

Integral Mounting Feet	Yes
Knockouts	No
Material	304 stainless steel
Finish	No. 3 intermediate polished
Cover Type	Single-door
Latch Type	Stainless steel clamps
Padlockable	No

## Agency Approvals

UL Listed File #	E32576
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/T8848CHSS.pdf>  
See store item page for other formats.