

TA0724S0203 Cut Sheet

CCEA TRACKALPHA-PRO series LED light bar, 921mm length, 120 VAC operating voltage, daylight white, 5000K, 46W, bracket mount, pigtail, anodized aluminum body, 9.8ft/3m cable length, IP67. Mounting bracket included.



For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA0724S0203>

Technical Specifications

Brand	CCEA
Item	LED light bar
Series	TRACKALPHA-PRO
Length	921mm
Operating Voltage	120 VAC
LED Color	Daylight white
Color Temperature	5000K
Mounting	Bracket
Connection	Pigtail
Power Consumption	46W
Body Material	Anodized aluminum
Cable Length	9.8ft/3m
IP Rating	IP67
Includes	Mounting bracket

Agency Approvals

UL Listed File #	NONE
UL Recognized File #	E526603
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/TA0724S0203.pdf>
See store item page for other formats.