

TA10-015-26-4X Cut Sheet



Stratus air conditioner, 1725 BTU/H, R-134a, 230 VAC operating voltage, 304 stainless steel housing, side mount. For use with NEMA/UL Type 4X enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA10-015-26-4X>

Technical Specifications

Brand	Stratus
Item	Air conditioner
Nominal Cooling Capacity	1725 BTU/H
Operating Voltage	230 VAC
Frequency	60 Hz
Running Current	2.7A
Refrigerant	R-134a
Height	22in
Width	11.8in
Depth	8.5in

Mounting	Side
Filter-Free	No
Filter Size	9 x 7.5in
Housing Material	304 stainless steel
For Use With	NEMA/UL Type 4X enclosures
Includes	Filter and mounting template and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	SA33404
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TA10-015-26-4X.pdf>
See store item page for other formats.