

TA10-027-46-4X Cut Sheet



Stratus air conditioner, 2680 BTU/H, R-134a, 460 VAC operating voltage, 304 stainless steel housing, side mount. For use with NEMA/UL Type 4X enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA10-027-46-4X>

Technical Specifications

Brand	Stratus
Item	Air conditioner
Nominal Cooling Capacity	2680 BTU/H
Operating Voltage	460 VAC
Frequency	60 Hz
Running Current	0.9A
Refrigerant	R-134a
Height	37.71in
Width	11.80in
Depth	9.5in

Mounting	Side
Filter-Free	No
Filter Size	11.3 x 7.3in
Housing Material	304 stainless steel
For Use With	NEMA/UL Type 4X enclosures
Includes	Filter and mounting template and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	SA33404
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/TA10-027-46-4X.pdf>
See store item page for other formats.