

TA10-050-46-12 Cut Sheet



Stratus air conditioner, 4390 BTU/H, R-422d, 460 VAC operating voltage, carbon steel housing, ANSI 61 gray, side mount. For use with NEMA/UL Type 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA10-050-46-12>

Technical Specifications

Brand	Stratus
Item	Air conditioner
Nominal Cooling Capacity	4390 BTU/H
Operating Voltage	460 VAC
Frequency	60 Hz
Running Current	1.4A
Refrigerant	R-422d
Height	44.6in
Width	11.8in
Depth	15in
Mounting	Side

Filter-Free	No
Filter Size	16.3 x 10.3in
Housing Material	Carbon steel
Color	ANSI 61 gray
For Use With	NEMA/UL Type 12 enclosures
Includes	Filter, mounting template, pre-cut gasket and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	SA33404
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TA10-050-46-12.pdf>
See store item page for other formats.