

TA10-060-16-4X Cut Sheet



Stratus air conditioner, 7580 BTU/H, R-422d, 115 VAC operating voltage, 304 stainless steel housing, side mount. For use with NEMA/UL Type 4X enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA10-060-16-4X>

Technical Specifications

Brand	Stratus
Item	Air conditioner
Nominal Cooling Capacity	7580 BTU/H
Operating Voltage	115 VAC
Frequency	60 Hz
Running Current	7.8A
Refrigerant	R-422d
Height	36in
Width	11.8in
Depth	15in
Mounting	Side
Filter-Free	No
Filter Size	16.3 x 10.3in
Housing Material	304 stainless steel
For Use With	NEMA/UL Type 4X enclosures
Includes	Filter and mounting template and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	SA33404
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document