

# TA10-060-46-04 Cut Sheet



Stratus air conditioner, 7580 BTU/H, R-422d, 460 VAC operating voltage, carbon steel housing, ANSI 61 gray, side mount. For use with NEMA/UL Type 4 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA10-060-46-04>

## Technical Specifications

|                                 |                 |
|---------------------------------|-----------------|
| <b>Brand</b>                    | Stratus         |
| <b>Item</b>                     | Air conditioner |
| <b>Nominal Cooling Capacity</b> | 7580 BTU/H      |
| <b>Operating Voltage</b>        | 460 VAC         |
| <b>Frequency</b>                | 60 Hz           |
| <b>Running Current</b>          | 1.8A            |
| <b>Refrigerant</b>              | R-422d          |
| <b>Height</b>                   | 44.6in          |
| <b>Width</b>                    | 11.8in          |
| <b>Depth</b>                    | 15in            |

|                         |                                                                                                                                               |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Mounting</b>         | Side                                                                                                                                          |
| <b>Filter-Free</b>      | No                                                                                                                                            |
| <b>Filter Size</b>      | 16.3 x 10.3in                                                                                                                                 |
| <b>Housing Material</b> | Carbon steel                                                                                                                                  |
| <b>Color</b>            | ANSI 61 gray                                                                                                                                  |
| <b>For Use With</b>     | NEMA/UL Type 4 enclosures                                                                                                                     |
| <b>Includes</b>         | Filter and mounting template and hardware                                                                                                     |
| <b>Dangerous Goods</b>  | <ul style="list-style-type: none"><li>• Packaging Instructions: 200</li><li>• UN Number: 3159</li><li>• Hazard Type: Compressed Gas</li></ul> |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | SA33404                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/TA10-060-46-04.pdf>  
See store item page for other formats.