

TA10-060-46-12 Cut Sheet



Stratus air conditioner, 7580 BTU/H, R-422d, 460 VAC operating voltage, carbon steel housing, ANSI 61 gray, side mount. For use with NEMA/UL Type 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA10-060-46-12>

Technical Specifications

| | |
|---------------------------------|---|
| Brand | Stratus |
| Item | Air conditioner |
| Nominal Cooling Capacity | 7580 BTU/H |
| Operating Voltage | 460 VAC |
| Frequency | 60 Hz |
| Running Current | 1.8A |
| Refrigerant | R-422d |
| Height | 44.6in |
| Width | 11.8in |
| Depth | 15in |
| Mounting | Side |
| Filter-Free | No |
| Filter Size | 16.3 x 10.3in |
| Housing Material | Carbon steel |
| Color | ANSI 61 gray |
| For Use With | NEMA/UL Type 12 enclosures |
| Includes | Filter, mounting template, pre-cut gasket and hardware |
| Dangerous Goods | <ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | SA33404 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |