

TA20-010-48D-04 Cut Sheet



Stratus air conditioner, 1500 BTU/H, R-134a, 48 VDC operating voltage, carbon steel housing, ANSI 61 gray, filter-free, side mount. For use with NEMA/UL Type 4 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA20-010-48D-04>

Technical Specifications

Brand	Stratus
Item	Air conditioner
Nominal Cooling Capacity	1500 BTU/H
Operating Voltage	48 VDC
Running Current	3.5A
Refrigerant	R-134a
Height	17in
Width	7in
Depth	7in
Mounting	Side
Filter-Free	Yes
Housing Material	Carbon steel
Color	ANSI 61 gray
For Use With	NEMA/UL Type 4 enclosures
Includes	Mounting template and hardware

Agency Approvals

UL Listed File #	SA33404
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document