

TA20-010-48D-12 Cut Sheet



Stratus air conditioner, 1500 BTU/H, R-134a, 48 VDC operating voltage, carbon steel housing, ANSI 61 gray, filter-free, side mount. For use with NEMA/UL Type 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA20-010-48D-12>

Technical Specifications

Brand	Stratus
Item	Air conditioner
Nominal Cooling Capacity	1500 BTU/H
Operating Voltage	48 VDC
Running Current	3.5A
Refrigerant	R-134a
Height	17in
Width	7in

Depth	7in
Mounting	Side
Filter-Free	Yes
Housing Material	Carbon steel
Color	ANSI 61 gray
For Use With	NEMA/UL Type 12 enclosures
Includes	Mounting template, pre-cut gasket and hardware

Agency Approvals

UL Listed File #	SA33404
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TA20-010-48D-12.pdf>
See store item page for other formats.