

TA20-020-16-12 Cut Sheet



Stratus air conditioner, 2705 BTU/H, R-134a, 115 VAC operating voltage, carbon steel housing, ANSI 61 gray, side mount. For use with NEMA/UL Type 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA20-020-16-12>

Technical Specifications

Brand	Stratus
Item	Air conditioner
Nominal Cooling Capacity	2705 BTU/H
Operating Voltage	115 VAC
Frequency	60 Hz
Running Current	4.1A
Refrigerant	R-134a
Height	20in
Width	10in
Depth	10in
Mounting	Side
Filter-Free	No
Filter Size	11 x 9in
Housing Material	Carbon steel
Color	ANSI 61 gray
For Use With	NEMA/UL Type 12 enclosures
Includes	Filter, mounting template, pre-cut gasket and hardware

Agency Approvals

UL Listed File #	SA33404
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document