

TA20-020-26-4X Cut Sheet



Stratus air conditioner, 2705 BTU/H, R-134a, 230 VAC operating voltage, 304 stainless steel housing, side mount. For use with NEMA/UL Type 4X enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA20-020-26-4X>

Technical Specifications

Brand	Stratus
Item	Air conditioner
Nominal Cooling Capacity	2705 BTU/H
Operating Voltage	230 VAC
Frequency	60 Hz
Running Current	2.0A
Refrigerant	R-134a
Height	20in

Width	10in
Depth	10in
Mounting	Side
Filter-Free	No
Filter Size	11 x 9in
Housing Material	304 stainless steel
For Use With	NEMA/UL Type 4X enclosures
Includes	Filter and mounting template and hardware

Agency Approvals

UL Listed File #	SA33404
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TA20-020-26-4X.pdf>
See store item page for other formats.