

# TAP-3000 Cut Sheet



NITRA pneumatic total air prep unit, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), 7-116 psi (0.5-8 bar) adjustable range, Rynite (PET) bowl, semi-automatic drain, clog indicator, manual shutoff valve, soft start valve, pressure switch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TAP-3000>

## Technical Specifications

Brand	NITRA
Working Fluid	Pneumatic
Item	Total air prep unit
Inlet Port	1/2in female NPT
Outlet Port	1/2in female NPT
Pressure Range	7-116 psi (0.5-8 bar) adjustable
Bowl Material	Rynite (PET)
Drain Type	Semi-automatic
Clog Indicator	Yes
Manual Shutoff Valve	Yes
Padlockable	Yes
Soft Start Valve	Yes
Pressure Switch	Yes
Electrical Connection	(1) 5-pin M12 quick-disconnect
Includes	Integral pressure gauge, locking adjustment knob and replaceable 20 micron filter element

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>