

TD250-02Z Cut Sheet



Schmersal heavy duty limit switch, side rotary lever with plastic roller, (2) N.C. contact(s), slow action, 122mm hole spacing, cast iron, (2) M25 x 1.5 cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TD250-02Z>

Technical Specifications

Brand	Schmersal
Item	Limit switch
Switch Type	Heavy duty
Actuator Type	Side rotary lever with plastic roller
Contact Type	(2) N.C.
Action	Slow action
Reset	No
Body Width	103mm
Mounting Hole Spacing	122mm
Material	Cast iron
IP Rating	IP65 IP66 IP67
Operating Temperature	-20 degrees to 60 degrees C
Connection	(2) M25 x 1.5 cable entry

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/TD250-02Z.pdf>
See store item page for other formats.