

# TD250-02/02Z Cut Sheet



Schmersal heavy duty limit switch, side rotary lever with plastic roller, (2) N.C. left and (2) N.C. right contact(s), slow action, 122mm hole spacing, cast iron, (2) M25 x 1.5 cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TD250-02/02Z>

## Technical Specifications

<b>Brand</b>	Schmersal
<b>Item</b>	Limit switch
<b>Switch Type</b>	Heavy duty
<b>Actuator Type</b>	Side rotary lever with plastic roller
<b>Contact Type</b>	(2) N.C. left and (2) N.C. right
<b>Action</b>	Slow action
<b>Reset</b>	No
<b>Body Width</b>	103mm
<b>Mounting Hole Spacing</b>	122mm
<b>Material</b>	Cast iron
<b>IP Rating</b>	IP65 IP66 IP67
<b>Operating Temperature</b>	-20 degrees to 60 degrees C
<b>Connection</b>	(2) M25 x 1.5 cable entry

## Agency Approvals

<b>UL Listed File #</b>	E57648
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
[https://cdn.automationdirect.com/static/drawings/2d/TD250-02\\_02Z.pdf](https://cdn.automationdirect.com/static/drawings/2d/TD250-02_02Z.pdf)  
See store item page for other formats.