

TD250-11/11Z Cut Sheet



Schmersal heavy duty limit switch, side rotary lever with plastic roller, (1) N.O./ (1) N.C. left and (1) N.O./ (1) N.C. right contact(s), slow action, 122mm hole spacing, cast iron, (2) M25 x 1.5 cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TD250-11/11Z>

Technical Specifications

Brand	Schmersal
Item	Limit switch
Switch Type	Heavy duty
Actuator Type	Side rotary lever with plastic roller
Contact Type	(1) N.O./ (1) N.C. left and (1) N.O./ (1) N.C. right
Action	Slow action
Reset	No
Body Width	103mm
Mounting Hole Spacing	122mm
Material	Cast iron
IP Rating	IP65 IP66 IP67
Operating Temperature	-20 degrees to 60 degrees C
Connection	(2) M25 x 1.5 cable entry

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/TD250-11_11Z.pdf
See store item page for other formats.