

TE20-015-17-04 Cut Sheet



Stratus CFC-free air-to-air heat exchanger, 22 W/deg C (12 W/deg F), 120 VAC operating voltage, 50/60 Hz, 0.37A running current, side mount, cold-rolled steel, ANSI 61 gray, powder coat finish. For use with NEMA/UL Type 4 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TE20-015-17-04>

Technical Specifications

| | |
|--------------------------|------------------------------------|
| Brand | Stratus |
| Item | CFC-free air-to-air Heat exchanger |
| Cooling Capacity | 22 W/deg C (12 W/deg F) |
| Operating Voltage | 120 VAC |
| Frequency | 50/60 Hz |
| Running Current | 0.37A |
| Mounting | Side |
| Housing Material | Cold-rolled steel |

| | |
|------------------------|---|
| Color | ANSI 61 gray |
| Finish | Powder coat |
| For Use With | NEMA/UL Type 4 enclosures |
| Includes | Mounting template and hardware |
| Dangerous Goods | <ul style="list-style-type: none">• Packaging Instruction: Y341• UN Number: UN1230• Hazard Type: Flammable Liquid |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | SA34086 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TE20-015-17-04.pdf>
See store item page for other formats.