

TE30-030-17-04 Cut Sheet



Stratus CFC-free air-to-air heat exchanger, 44 W/deg C (24 W/deg F), 120 VAC operating voltage, 50/60 Hz, 0.37A running current, side mount, cold-rolled steel, ANSI 61 gray, powder coat finish. For use with NEMA/UL Type 4 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TE30-030-17-04>

Technical Specifications

Brand	Stratus
Item	CFC-free air-to-air Heat exchanger
Cooling Capacity	44 W/deg C (24 W/deg F)
Operating Voltage	120 VAC
Frequency	50/60 Hz
Running Current	0.37A
Mounting	Side
Housing Material	Cold-rolled steel

Color	ANSI 61 gray
Finish	Powder coat
For Use With	NEMA/UL Type 4 enclosures
Includes	Mounting template and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instruction: Y341• UN Number: UN1230• Hazard Type: Flammable Liquid

Agency Approvals

UL Listed File #	SA34086
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TE30-030-17-04.pdf>
See store item page for other formats.