

# TE30-030-24D-04 Cut Sheet



Stratus CFC-free air-to-air heat exchanger, 44 W/deg C (24 W/deg F), 24 VDC operating voltage, 0.80A running current, side mount, cold-rolled steel, ANSI 61 gray, powder coat finish. For use with NEMA/UL Type 4 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TE30-030-24D-04>

## Technical Specifications

Brand	Stratus
Item	CFC-free air-to-air Heat exchanger
Cooling Capacity	44 W/deg C (24 W/deg F)
Operating Voltage	24 VDC
Running Current	0.80A
Mounting	Side
Housing Material	Cold-rolled steel
Color	ANSI 61 gray
Finish	Powder coat
For Use With	NEMA/UL Type 4 enclosures
Includes	Mounting template and hardware
Dangerous Goods	<ul style="list-style-type: none"><li>• Packaging Instruction: Y341</li><li>• UN Number: UN1230</li><li>• Hazard Type: Flammable Liquid</li></ul>

## Agency Approvals

UL Listed File #	SA34086
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/TE30-030-24D-04.pdf>  
See store item page for other formats.