

TE40-050-17-4X Cut Sheet



Stratus CFC-free air-to-air heat exchanger, 71.6 W/deg C (40 W/deg F), 120 VAC operating voltage, 50/60 Hz, 0.47A running current, side mount, 304 stainless steel. For use with NEMA/UL Type 4X enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TE40-050-17-4X>

Technical Specifications

Brand	Stratus
Item	CFC-free air-to-air Heat exchanger
Cooling Capacity	71.6 W/deg C (40 W/deg F)
Operating Voltage	120 VAC
Frequency	50/60 Hz
Running Current	0.47A
Mounting	Side
Housing Material	304 stainless steel
For Use With	NEMA/UL Type 4X enclosures
Includes	Mounting template and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instruction: Y341• UN Number: UN1230• Hazard Type: Flammable Liquid

Agency Approvals

UL Listed File #	SA34086
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document