

# TE40-050-24D-04 Cut Sheet



Stratus CFC-free air-to-air heat exchanger, 71.6 W/deg C (40 W/deg F), 24 VDC operating voltage, 1.94A running current, side mount, cold-rolled steel, ANSI 61 gray, powder coat finish. For use with NEMA/UL Type 4 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TE40-050-24D-04>

## Technical Specifications

|                          |   |
|--------------------------|---|
| <b>Brand</b>             | Stratus   |
| <b>Item</b>              | CFC-free air-to-air Heat exchanger  |
| <b>Cooling Capacity</b>  | 71.6 W/deg C (40 W/deg F)   |
| <b>Operating Voltage</b> | 24 VDC  |
| <b>Running Current</b>   | 1.94A   |
| <b>Mounting</b>          | Side  |
| <b>Housing Material</b>  | Cold-rolled steel   |
| <b>Color</b>             | ANSI 61 gray  |
| <b>Finish</b>            | Powder coat   |
| <b>For Use With</b>      | NEMA/UL Type 4 enclosures   |
| <b>Includes</b>          | Mounting template and hardware  |
| <b>Dangerous Goods</b>   | <ul style="list-style-type: none"><li>• Packaging Instruction: Y341</li><li>• UN Number: UN1230</li><li>• Hazard Type: Flammable Liquid</li></ul> |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | SA34086                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |