

TFFN18GN Cut Sheet



Atlas Wire TFFN building wire, single conductor, 18 AWG, 16-stranded, bare copper, PVC conductor insulation material, green, nylon jacket, clear, 600V, 500ft spool.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TFFN18GN>

Technical Specifications

Brand	Atlas Wire
Item	Wire
Wire/Cable Type	TFFN
UL Wire/Cable Type	TFFN and MTW
Applicable Standards	UL 66, UL 758, UL 1063, UL 1408, UL 1452, UL 1316 and C22.2 No. 210
Application	Building
Flexibility	Flexible
Voltage Rating	600V
Conductors	Single conductor
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Green
Jacket Material	Nylon
Jacket Color	Clear
Nominal Overall Cable Diameter	0.09in
Bulk Length	500ft spool

Agency Approvals

UL Listed File #	E156878
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement