

THHN10WH Cut Sheet



Atlas Wire THHN building wire, single conductor, 10 AWG, 19-stranded, bare copper, PVC conductor insulation material, white, nylon jacket, clear, 600V, 500ft spool.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THHN10WH>

Technical Specifications

Brand	Atlas Wire	Conductor Stranding	19-stranded
Item	Wire	Conductor Material	Bare copper
Wire/Cable Type	THHN	Conductor Insulation Material	PVC
UL Wire/Cable Type	THHN, THWN-2 and MTW	Conductor Insulation Color	White
Applicable Standards	UL 1063, UL 758, CSA C22.2 No. 210 and UL 1317	Jacket Material	Nylon
Application	Building	Jacket Color	Clear
Flexibility	Flexible	Nominal Overall Cable Diameter	0.166in
Voltage Rating	600V	Bulk Length	500ft spool
Conductors	Single conductor		
Conductor Size	10 AWG		

Agency Approvals

UL Listed File #	E80255
UL Recognized File #	E25635
UL Hazardous File #	None
CE	None
CSA File #	150272
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement