

THHN14BW Cut Sheet



Atlas Wire THHN building wire, single conductor, 14 AWG, 19-stranded, bare copper, PVC conductor insulation material, blue with white stripe, nylon jacket, clear, 600V, 500ft spool.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THHN14BW>

Technical Specifications

| | |
|-----------------------------|--|
| Brand | Atlas Wire |
| Item | Wire |
| Wire/Cable Type | THHN |
| UL Wire/Cable Type | THHN, THWN-2 and MTW |
| Applicable Standards | UL 1063, UL 758, UL 1452, UL 1316, UL 1408 and CSA C22.2 No. 210 |
| Application | Building |
| Flexibility | Flexible |
| Voltage Rating | 600V |
| Conductors | Single conductor |
| Conductor Size | 14 AWG |

| | |
|---------------------------------------|------------------------|
| Conductor Stranding | 19-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | PVC |
| Conductor Insulation Color | Blue with white stripe |
| Jacket Material | Nylon |
| Jacket Color | Clear |
| Nominal Overall Cable Diameter | 0.113in |
| Bulk Length | 500ft spool |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E80255 |
| UL Recognized File # | E25635 |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 150272 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |