

# THHN14YL Cut Sheet



Atlas Wire THHN building wire, single conductor, 14 AWG, 19-stranded, bare copper, PVC conductor insulation material, yellow, nylon jacket, clear, 600V, 500ft spool.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THHN14YL>

## Technical Specifications

|                             |  |
|-----------------------------|--|
| <b>Brand</b>                | Atlas Wire   |
| <b>Item</b>                 | Wire   |
| <b>Wire/Cable Type</b>      | THHN   |
| <b>UL Wire/Cable Type</b>   | THHN, THWN-2 and MTW   |
| <b>Applicable Standards</b> | UL 1063, UL 758, UL 1452, UL 1316, UL 1408 and CSA C22.2 No. 210 |
| <b>Application</b>          | Building   |
| <b>Flexibility</b>          | Flexible   |
| <b>Voltage Rating</b>       | 600V   |
| <b>Conductors</b>           | Single conductor   |
| <b>Conductor Size</b>       | 14 AWG   |

|                                       |             |
|---------------------------------------|-------------|
| <b>Conductor Stranding</b>            | 19-stranded |
| <b>Conductor Material</b>             | Bare copper |
| <b>Conductor Insulation Material</b>  | PVC         |
| <b>Conductor Insulation Color</b>     | Yellow      |
| <b>Jacket Material</b>                | Nylon       |
| <b>Jacket Color</b>                   | Clear       |
| <b>Nominal Overall Cable Diameter</b> | 0.113in     |
| <b>Bulk Length</b>                    | 500ft spool |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E123774   |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |