


THMJ-A01L04-01 Cut Sheet



ProSense temperature sensor, Type J thermocouple, armor adjustable immersion probe, grounded, 1/4in insertion length, 3/16in probe diameter, stainless steel sheath, bayonet cap process connection, 4ft 20 AWG wire leads.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMJ-A01L04-01>

Technical Specifications

Brand	ProSense
Item	Temperature sensor
Sensor Element	Type J thermocouple
Sensor Type	Armor adjustable immersion probe
Accuracy	Standard limits of error
Junction Type	Grounded
Insertion Length	1/4in
Probe Diameter	3/16in

Sheath Material	Stainless steel
Process Connection	Bayonet cap
Bayonet Cap	7/16in inside diameter single slot
Electrical Connection	4ft 20 AWG wire leads
Conductor Insulation Material	Fiberglass and flexible armor
Temperature Sensing Range	32 to 900 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/THMJ-A01L04-01.pdf>
See store item page for other formats.