

THMJ-HT34-01 Cut Sheet



ProSense temperature sensor, Type J thermocouple, heat trace probe, ungrounded junction, stainless steel sheath, aluminum screw cover head with terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMJ-HT34-01>

Technical Specifications

Brand	ProSense
Item	Temperature sensor
Sensor Element	Type J thermocouple
Sensor Type	Heat trace probe
Accuracy	Standard limits of error
Junction Type	Ungrounded
Sheath Material	Stainless steel
Sensor Insulation	Fiberglass
Electrical Connection	Aluminum screw cover head with terminals
Temperature Sensing Range	0 to 900 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/THMJ-HT34-01.pdf>
See store item page for other formats.