

THMJ-M01L06-01 Cut Sheet



ProSense temperature sensor, Type J thermocouple, magnet mount sensor, exposed junction, 10 lb pull magnet process connection, 6ft 20 AWG wire leads.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMJ-M01L06-01>

Technical Specifications

Brand	ProSense
Item	Temperature sensor
Sensor Element	Type J thermocouple
Sensor Type	Magnet mount sensor
Accuracy	Standard limits of error
Junction Type	Exposed
Sensor Insulation	Ceramic
Process Connection	10 lb pull magnet
Electrical Connection	6ft 20 AWG wire leads
Conductor Insulation Material	Closed cell sponge rubber
Temperature Sensing Range	0 to 600 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/THMJ-M01L06-01.pdf>
See store item page for other formats.