

# THMJ-M01L06-01 Cut Sheet



ProSense temperature sensor, Type J thermocouple, magnet mount sensor, exposed junction, 10 lb. pull magnet process connection, 6ft 20 AWG wire leads.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMJ-M01L06-01>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Temperature sensor
<b>Sensor Element</b>	Type J thermocouple
<b>Sensor Type</b>	Magnet mount sensor
<b>Accuracy</b>	Standard limits of error
<b>Junction Type</b>	Exposed
<b>Sensor Insulation</b>	Ceramic
<b>Process Connection</b>	10 lb. pull magnet
<b>Electrical Connection</b>	6ft 20 AWG wire leads
<b>Conductor Insulation Material</b>	Fiberglass and stainless steel overbraid
<b>Temperature Sensing Range</b>	0 to 600 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>