

# THMJ-P06-01 Cut Sheet

ProSense temperature sensor, Type J thermocouple, attached plug probe, ungrounded, 6in insertion length, 1/8in probe diameter, stainless steel sheath, 2-pin miniature size plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMJ-P06-01>



## Technical Specifications

Brand	ProSense
Item	Temperature sensor
Sensor Element	Type J thermocouple
Sensor Type	Attached plug probe
Accuracy	Standard limits of error
Junction Type	Ungrounded
Insertion Length	6in
Probe Diameter	1/8in
Sheath Material	Stainless steel
Sensor Insulation	Magnesium oxide (MgO)
Electrical Connection	2-pin miniature size plug
Temperature Sensing Range	32 to 970 deg F
Additional Information	Purchase mating jack and mounting fitting separately

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>