

THMJ-P06-02 Cut Sheet



ProSense temperature sensor, Type J thermocouple, attached plug probe, ungrounded, 6in insertion length, 1/4in probe diameter, stainless steel sheath, 2-pin standard size plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMJ-P06-02>

Technical Specifications

| | |
|----------------------------------|--|
| Brand | ProSense |
| Item | Temperature sensor |
| Sensor Element | Type J thermocouple |
| Sensor Type | Attached plug probe |
| Accuracy | Standard limits of error |
| Junction Type | Ungrounded |
| Insertion Length | 6in |
| Probe Diameter | 1/4in |
| Sheath Material | Stainless steel |
| Sensor Insulation | Magnesium oxide (MgO) |
| Electrical Connection | 2-pin standard size plug |
| Temperature Sensing Range | 32 to 1330 deg F |
| Additional Information | Purchase mating jack and mounting fitting separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | None |