

THMJ-R01-01 Cut Sheet



ProSense temperature sensor, Type J thermocouple, room sensor, ungrounded, plastic ventilated housing, metal wall mounting subplate process connection, terminal strip.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMJ-R01-01>

Technical Specifications

Brand	ProSense
Item	Temperature sensor
Sensor Element	Type J thermocouple
Sensor Type	Room sensor
Accuracy	Standard limits of error
Junction Type	Ungrounded
Housing Material	Plastic ventilated
Process Connection	Metal wall mounting subplate
Electrical Connection	Terminal strip
Temperature Sensing Range	32 to 185 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/THMJ-R01-01.pdf>
See store item page for other formats.