

THMK-N38P14-02 Cut Sheet



ProSense temperature sensor, Type K thermocouple, threaded bolt sensor, ungrounded junction, 3/8in bolt length, 3/16in tip, stainless steel sheath, 1/4-28 UNF process connection, 6ft 24 AWG wire leads.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMK-N38P14-02>

Technical Specifications

Brand	ProSense
Item	Temperature sensor
Sensor Element	Type K thermocouple
Sensor Type	Threaded bolt sensor
Accuracy	Standard limits of error
Junction Type	Ungrounded
Bolt Length	3/8in
Tip Length	3/16in
Tip Diameter	3/16in
Sheath Material	Stainless steel
Sensor Insulation	Fiberglass
Process Connection	1/4-28 UNF
Electrical Connection	6ft 24 AWG wire leads
Conductor Insulation Material	Fiberglass and stainless steel overbraid
Temperature Sensing Range	0 to 900 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document