

THMK-N38P14-02 Cut Sheet



ProSense temperature sensor, Type K thermocouple, threaded bolt sensor, ungrounded junction, 3/8in bolt length, 3/16in tip, stainless steel sheath, 1/4-28 UNF process connection, 6ft 24 AWG wire leads.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMK-N38P14-02>

Technical Specifications

| | |
|----------------|--------------------------|
| Brand | ProSense |
| Item | Temperature sensor |
| Sensor Element | Type K thermocouple |
| Sensor Type | Threaded bolt sensor |
| Accuracy | Standard limits of error |
| Junction Type | Ungrounded |
| Bolt Length | 3/8in |
| Tip Length | 3/16in |
| Tip Diameter | 3/16in |

| | |
|-------------------------------|--|
| Sheath Material | Stainless steel |
| Sensor Insulation | Fiberglass |
| Process Connection | 1/4-28 UNF |
| Electrical Connection | 6ft 24 AWG wire leads |
| Conductor Insulation Material | Fiberglass and stainless steel overbraid |
| Temperature Sensing Range | 0 to 900 deg F |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/THMK-N38P14-02.pdf>
See store item page for other formats.