

THMK-P06-01 Cut Sheet

ProSense temperature sensor, Type K thermocouple, attached plug probe, ungrounded, 6in insertion length, 1/8in probe diameter, stainless steel sheath, 2-pin miniature size plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMK-P06-01>



Technical Specifications

Brand	ProSense
Item	Temperature sensor
Sensor Element	Type K thermocouple
Sensor Type	Attached plug probe
Accuracy	Standard limits of error
Junction Type	Ungrounded
Insertion Length	6in
Probe Diameter	1/8in
Sheath Material	Stainless steel
Sensor Insulation	Magnesium oxide (MgO)
Electrical Connection	2-pin miniature size plug
Temperature Sensing Range	32 to 1700 deg F
Additional Information	Purchase mating jack and mounting fitting separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/THMK-P06-01.pdf>
See store item page for other formats.