

THMK-SJ Cut Sheet



ProSense Type K thermocouple connector, standard round pin jack, 400 deg F (200 deg C), glass filled thermoplastic body, yellow, thermocouple material pins, 32 AWG to 14 AWG wire size range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMK-SJ>

Technical Specifications

Brand	ProSense
Item	Type K thermocouple Connector
Connector Type	Standard round pin jack
Operating Temperature	400 deg F (200 deg C)
Body Material	Glass filled thermoplastic
Body Color	Yellow
Pin Material	Thermocouple material
Wire Size Range	32 AWG to 14 AWG

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/THMK-SJ.pdf>
See store item page for other formats.