

# THMT-MPJ Cut Sheet



ProSense Type T thermocouple connector, miniature flat pin panel jack, 400 deg F (200 deg C), glass filled thermoplastic body, blue, thermocouple material pins, 32 AWG to 14 AWG wire size range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMT-MPJ>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Type T thermocouple Connector
<b>Connector Type</b>	Miniature flat pin panel jack
<b>Operating Temperature</b>	400 deg F (200 deg C)
<b>Body Material</b>	Glass filled thermoplastic
<b>Body Color</b>	Blue
<b>Pin Material</b>	Thermocouple material
<b>Wire Size Range</b>	32 AWG to 14 AWG

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/THMT-MPJ.pdf>  
See store item page for other formats.