


THMT-T12L06-01 Cut Sheet



ProSense temperature sensor, Type T thermocouple, lead wire transition probe, ungrounded, 12in insertion length, 1/8in probe diameter, stainless steel sheath, 6ft 20 AWG wire leads.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMT-T12L06-01>

Technical Specifications

| | |
|--------------------------------------|--|
| Brand | ProSense |
| Item | Temperature sensor |
| Sensor Element | Type T thermocouple |
| Sensor Type | Lead wire transition probe |
| Accuracy | Standard limits of error |
| Junction Type | Ungrounded |
| Insertion Length | 12in |
| Probe Diameter | 1/8in |
| Sheath Material | Stainless steel |
| Sensor Insulation | Magnesium oxide (MgO) |
| Electrical Connection | 6ft 20 AWG wire leads |
| Conductor Insulation Material | Fiberglass and stainless steel overbraid |
| Temperature Sensing Range | -328 to 700 deg F |
| Additional Information | Purchase mounting fitting separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |