

THMWJ-16-1U-P-1 Cut Sheet



TE Wire & Cable Type J thermocouple extension wire, unshielded, 2 conductors, 16 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-16-1U-P-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Wire
Sensor Type	Type J thermocouple
Wire/Cable Type	Extension
Application	Temperature
Flexibility	Semi-flexible
Conductors	2 conductors
Conductor Size	16 AWG
Conductor Stranding	Solid
Conductor Material	Iron and copper-nickel
Conductor Insulation Material	PVC
Conductor Insulation Color	White and red

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.188in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 1105ft = 14 x 7in Reel, 1106 to 1575ft = 14 x 10in Reel, 1576 to 2415ft = 16 x 10in Reel, 2416 to 3375ft = 18 x 10in Reel, 3376 to 4390ft = 18 x 13in Reel, 4391 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	none
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	none
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement